




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




PART NO	PIN	A	B
C-JC2.0-1-W2P62	2	2.00	4.5
C-JC2.0-1-W3P62	3	4.00	6.5
C-JC2.0-1-W4P62	4	6.00	8.5
C-JC2.0-1-W5P62	5	8.00	10.5
C-JC2.0-1-W6P62	6	10.00	12.5
C-JC2.0-1-W7P62	7	12.00	14.5
C-JC2.0-1-W8P62	8	14.00	16.5
C-JC2.0-1-W9P62	9	16.00	18.5
C-JC2.0-1-W10P62	10	18.00	20.5
C-JC2.0-1-W11P62	11	20.00	22.5
C-JC2.0-1-W12P62	12	22.00	24.5
C-JC2.0-1-W13P62	13	24.00	26.5
C-JC2.0-1-W14P62	14	26.00	28.5
C-JC2.0-1-W15P62	15	28.00	30.5
C-JC2.0-1-W16P62	16	30.00	32.5
C-JC2.0-1-W17P62	17	32.00	34.5
C-JC2.0-1-W18P62	18	34.00	36.5
C-JC2.0-1-W19P62	19	36.00	38.5
C-JC2.0-1-W20P62	20	38.00	40.5

技术指标(Technical Index):

- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):250V AC,DC.
- 3.耐电压(Withstanding Voltage):1000V AC/minute.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 6.额定电流(Rated Current): 2A AC,DC.

材料:

- 1.塑胶:PA66 白色



TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO. C-JC2.0-1-WNP62	TITLE: JC20 WTB等插板胶芯		
X.X±0.20					
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm				
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1