









SPECIFICATION:
1.MATERIAL:
HOUSING: LCP UL 94V-0
COLOR:BLACK
CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm
PEG:C2680R-H,T=0.50mm
2.FINISH:
CONTACT:1u"/3u"/5u"/15u" GOLDPLATING ON CONTACT AREA
100u" TIN PLATING ON SOLDER TAILS
30u" NICKEL UNDERPLATING OVER ALL
PEG: 100u" TIN PLATING ON SOLDER TAILS
30u" NICKEL UNDERPLATING OVER ALL



环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	.X°±3°	PART NO.	TITLE: SATA 7+15P 母座	
.XX±0.20	.XX°±2°	JXT-SATA07-M22PS	DIP 180° 双排双鱼叉加长型针长2.7	
.XXX±0.05	.XXX°±0.5°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		
MATERILA	---	APPD: Ava		
FINISH	---			
				SCALE SHEET N:A 1/1