


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



技术指标(Technical Index):

- 1.工作温度(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):100V DC/AC(rms).
- 3.额定电流(Rated current):1.0A AC,DC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Dielectricwithstanding voltage):500V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.
- 7.适用线规(Apply to gauge):AWG#26~#30.

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO.	TITLE:		
X.X±0.20		B-ZH1.5-1-GE2DP2	ZH1.5 WTB公头端子		
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	---	APPD: Ava		N:A	1/1