



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

SPECIFICATION:

1.MATERIAL:

HOUSING: LCP UL 94V-0

COLOR: BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:








CONTACT:1u"3u"5u"15u" GOLD PLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL



RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE:±0.05

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	.X"±3"	PART NO.	TITLE: SATA 7+15P 母座	
.XX±0.20	.XX"±2"	JXT-SATA03-A2-M22PX	SMT H:3.50 板上侧插式	
.XXX±0.05	.XXX"±0.5"	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		
MATERILA	---	APPD: Ava		
FINISH	---			
				SCALE SHEET N:A 1/1