





技术指标(Technical Index):

- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):250V AC,DC.
- 3.耐电压(Withstanding Voltage):1000V AC/minute.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 6.额定电流(Rated Current):2.5A AC,DC.

材料:


- 1.塑胶:PA66 白色



Assembly View (DIM FYI)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

PART NO	PIN	A	B
C-SCN2.5-1-W2P62	2	2.50	6.5
C-SCN2.5-1-W3P62	3	5.00	9.0
C-SCN2.5-1-W4P62	4	7.50	11.5
C-SCN2.5-1-W5P62	5	10.00	14.0
C-SCN2.5-1-W6P62	6	12.50	16.5
C-SCN2.5-1-W7P62	7	15.00	19.0
C-SCN2.5-1-W8P62	8	17.50	21.5
C-SCN2.5-1-W9P62	9	20.00	24.0
C-SCN2.5-1-W10P62	10	22.50	26.5
C-SCN2.5-1-W11P62	11	25.00	29.0
C-SCN2.5-1-W12P62	12	27.50	31.5
C-SCN2.5-1-W13P62	13	30.00	34.0
C-SCN2.5-1-W14P62	14	32.50	36.5
C-SCN2.5-1-W15P62	15	35.00	39.0
C-SCN2.5-1-W16P62	16	37.50	41.5



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X:±0.50	±1°	PART NO.	TITLE:		
X.X±0.20		C-SCN2.5-1-WNP62	SCN2.5 WTB直插板胶芯		
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	---	APPD: Ava		N:A	1/1