




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




PART NO	PIN	A	B
C-SZN1.5-1-W2P62	2	1.50	4.0
C-SZN1.5-1-W3P62	3	3.00	5.5
C-SZN1.5-1-W4P62	4	4.50	7.0
C-SZN1.5-1-W5P62	5	6.00	8.5
C-SZN1.5-1-W6P62	6	7.50	10.0
C-SZN1.5-1-W7P62	7	9.00	11.5
C-SZN1.5-1-W8P62	8	10.50	13.0
C-SZN1.5-1-W9P62	9	12.00	14.5
C-SZN1.5-1-W10P62	10	13.50	16.0
C-SZN1.5-1-W11P62	11	15.00	17.5
C-SZN1.5-1-W12P62	12	16.50	19.0
C-SZN1.5-1-W13P62	13	18.00	20.5
C-SZN1.5-1-W14P62	14	19.50	22.0
C-SZN1.5-1-W15P62	15	21.00	23.5
C-SZN1.5-1-W16P62	16	22.50	25.0
C-SZN1.5-1-W17P62	17	24.00	26.5
C-SZN1.5-1-W18P62	18	25.50	28.0
C-SZN1.5-1-W19P62	19	27.00	29.5
C-SZN1.5-1-W20P62	20	28.50	31.0

技术指标(Technical Index):

- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):50V AC,DC.
- 3.耐电压(Withstanding Voltage):500V AC/minute.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 6.额定电流(Rated Current):0.7A AC,DC.

材料:

- 1.塑胶:PA66 白色



TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X. ± 0.50	$\pm 1^{\circ}$	PART NO.	TITLE:		
X.X ± 0.20		C-SZN1.5-1-WNP62	SZN1.5 WTB直插板胶芯		
X.XX ± 0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	---	APPD: Ava		N:A	1/1