


| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
|      |         |             |      |        |
|      |         |             |      |        |




| PART NO           | PIN | A     | B    |
|-------------------|-----|-------|------|
| C-SAN2.0-1-W2P62  | 2   | 2.00  | 5.3  |
| C-SAN2.0-1-W3P62  | 3   | 4.00  | 7.3  |
| C-SAN2.0-1-W4P62  | 4   | 6.00  | 9.3  |
| C-SAN2.0-1-W5P62  | 5   | 8.00  | 11.3 |
| C-SAN2.0-1-W6P62  | 6   | 10.00 | 13.3 |
| C-SAN2.0-1-W7P62  | 7   | 12.00 | 15.3 |
| C-SAN2.0-1-W8P62  | 8   | 14.00 | 17.3 |
| C-SAN2.0-1-W9P62  | 9   | 16.00 | 19.3 |
| C-SAN2.0-1-W10P62 | 10  | 18.00 | 21.3 |
| C-SAN2.0-1-W11P62 | 11  | 20.00 | 23.3 |
| C-SAN2.0-1-W12P62 | 12  | 22.00 | 25.3 |
| C-SAN2.0-1-W13P62 | 13  | 24.00 | 27.3 |
| C-SAN2.0-1-W14P62 | 14  | 26.00 | 29.3 |
| C-SAN2.0-1-W15P62 | 15  | 28.00 | 31.3 |
| C-SAN2.0-1-W16P62 | 16  | 30.00 | 33.3 |
| C-SAN2.0-1-W17P62 | 17  | 32.00 | 35.3 |
| C-SAN2.0-1-W18P62 | 18  | 34.00 | 37.3 |
| C-SAN2.0-1-W19P62 | 19  | 36.00 | 39.3 |
| C-SAN2.0-1-W20P62 | 20  | 38.00 | 41.3 |

- 技术指标(Technical Index):
- 1.温度范围(Temperature range):-25℃~+85℃.
  - 2.额定电压(Rated voltage):250V AC,DC.
  - 3.耐电压(Withstanding Voltage):1000V AC/minute.
  - 4.接触电阻(Contact resistance):≤20mΩ.
  - 5.绝缘电阻(Insulation resistance):≥1000MΩ.
  - 6.额定电流(Rated Current):2A AC,DC.

材料:

- 1.塑胶:PA66 白色



| TOLERANCE |       | <div><div><div></div></div>深圳聚兴泰电子科技有限公司</div> <div>Shenzhen Juxingtai Electronic Technology Co., Ltd</div> |  |                                                                                       |       |       |
|-----------|-------|-------------------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------|-------|-------|
| X.±0.50   | ±1°   | PART NO.                                                                                                    |  | TITLE:                                                                                |       |       |
| X.X±0.20  |       | C-SAN2.0-1-WNP62                                                                                            |  | SAN2.0 WTB直插板胶芯                                                                       |       |       |
| X.XX±0.10 |       | DESIGN: Ethan                                                                                               |  | MANUFACTURE DWG                                                                       |       |       |
| UNITS     | mm    | CHED: Olvia                                                                                                 |  |  | SCALE | SHEET |
| MATERILA  | — — — | APPD: Ava                                                                                                   |  |                                                                                       | N:A   | 1/1   |