




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATION:

1.MATERIAL:


HOUSING:LCP 30% G/F UL 94V-0
 COLOR:BLACK
 CONTACT:BRASS C2680R-H,T=0.25mm

2.FINISH:

CONTACT:1u",3u",5u",15u"30u"GOLD PLATING ON CONTACT AREA
 100u" MIN.TIN PLATING ON SOLDERTAILS
 40u" MIN.NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:

CURRENT RATING:1.5 AMPERE PER CONTACT
 CONTACT RESISTANCE:30 MILLIOHMS MAX
 INSULATION RESISTANCE:1000 MEGOHMS MIN
 DIELECTRIC WITH STANDING VOVTAG:500 VDC
 OPERATING TEMPERATURE: -40°C ~ +85°C



环保要求		产品必须符合ROHS要求		
2	Terminal	BRASS C2680R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	.X"±3"	PART NO.	TITLE: SATA 7+15P 夹角公座	
.XX±0.20	.XX"±2"	JXT-SATA02-G22PX	夹板1.0七个孔	
.XXX±0.05	.XXX"±0.5"	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		
MATERILA	---	APPD: Ava		
FINISH	---			SCALE N:A
				SHEET 1/1