




SPECIFICATION:

1.MATERIAL:

HOUSING: LCP E130i 30% G/F UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.20mm

2.FINISH:


CONTACT:1u"/3u"/5u"/15u"GOLD PLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL



RECOMMENDED PCB LAYOUT
UNLESS TOLERANCE: +/ - 0.05

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd	
.X±0.30	.X°±3°	PART NO.	TITLE: SATA 7+15P
.XX±0.20	.XX°±2°	JXT-SATA08-M22PX	直立式SMT 带接地片
.XXX±0.05	.XXX°±0.5°	DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm	CHED: Olvia	
MATERILA	---	APPD: Ava	
FINISH	---		
			SCALE SHEET N:A 1/1