










RECOMMEND PCB LAYOUT
PCB TOLERANCE:±0.05

SPECIFICATION:

1.MATERIAL:

HOUSING:LCP UL 94V-0

COLOR:BLACK

CONTACT:BRASS C2680-H,T=0.25mm

PEG:BRASS C2680R-H,T=0.30mm

2.FINISH:

CONTACT:1u"/3u"/5u"/15u" GOLD/TIN PLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDER TAILS

50u" NICKEL UNDERPLATING OVERALL

PEG:100u" TIN PLATING ON SOLDER TAILS

50u" NICKEL UNDERPLATING OVERALL

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Brass C2680R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	.X°±3°	PART NO.	TITLE:	
.XX±0.20	.XX°±2°	JXT-SATA03-GS7P	SATA 7P 公座 三面包 SMT型	
.XXX±0.05	.XXX°±0.5°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		
MATERILA	---	APPD: Ava		
FINISH	---			
			SCALE	SHEET
			N:A	1/1