




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




PART NO	PIN	A	B
C-JC1.5-1-W2P62	2	1.5	4.0
C-JC1.5-1-W3P62	3	3.0	5.5
C-JC1.5-1-W4P62	4	4.5	7.0
C-JC1.5-1-W5P62	5	6.0	8.5
C-JC1.5-1-W6P62	6	7.5	10.0
C-JC1.5-1-W7P62	7	9.0	11.5
C-JC1.5-1-W8P62	8	10.5	13.0
C-JC1.5-1-W9P62	9	12.0	14.5
C-JC1.5-1-W10P62	10	13.5	16.0
C-JC1.5-1-W11P62	11	15.0	17.5
C-JC1.5-1-W12P62	12	16.5	19.0
C-JC1.5-1-W13P62	13	18.0	20.5
C-JC1.5-1-W14P62	14	19.5	22.0
C-JC1.5-1-W15P62	15	21.0	23.5
C-JC1.5-1-W16P62	16	22.5	25.0
C-JC1.5-1-W17P62	17	24.0	26.5
C-JC1.5-1-W18P62	18	25.5	28.0
C-JC1.5-1-W19P62	19	27.0	29.5
C-JC1.5-1-W20P62	20	28.5	31.0

技术指标(Technical Index):

- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):50V AC,DC.
- 3.耐电压(Withstanding Voltage):500V AC/minute.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 6.额定电流(Rated Current): 0.7A AC,DC.

材料:

- 1.塑胶:PA66 白色



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X. ± 0.50	$\pm 1^{\circ}$	PART NO.	TITLE:	
X.X ± 0.20		C-JC1.5-1-WNP62	JC15 WTB等插板胶芯	
X.XX ± 0.10		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		
MATERILA	---	APPD: Ava		
FINISH	---		SCALE	SHEET
			N:A	1/1