



SPECIFICATION:

1.MATERIAL:

HOUSING:LCP UL 94V-0

COLOR:BLACK

CONTACT:PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG:BRASS C2680R-H,T=0.30mm

2.FINISH:

CONTACT:1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA








100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL


PEG:100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK



TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	.X'±3"	PART NO.	TITLE: SATA 7+15P 母座		
.XX±0.20	.XX'±2"	JXT-SATA07-A2-M22PX	SMT H:6.74 板上型		
.XXX±0.05	.XXX'±0.5"	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1
FINISH	— — —				