






技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. 额定电压: 100V AC, DC.
3. 耐电压: 500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 500\text{M}\Omega$.
6. 额定电流: 1A AC, DC.


材料:

1. 塑胶: PA66 白色




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

PART NO	PIN	A	B	C
C-ZH1.5-1-GFW2P62	2	1.50	3.40	4.5
C-ZH1.5-1-GFW3P62	3	3.00	4.90	6.0
C-ZH1.5-1-GFW4P62	4	4.50	6.40	7.5
C-ZH1.5-1-GFW5P62	5	6.00	7.90	9.0
C-ZH1.5-1-GFW6P62	6	7.50	9.40	10.5
C-ZH1.5-1-GFW7P62	7	9.00	10.90	12.0
C-ZH1.5-1-GFW8P62	8	10.50	12.40	13.5
C-ZH1.5-1-GFW9P62	9	12.00	13.90	15.0
C-ZH1.5-1-GFW10P62	10	13.50	15.40	16.5
C-ZH1.5-1-GFW11P62	11	15.00	16.90	18.0
C-ZH1.5-1-GFW12P62	12	16.50	18.40	19.5
C-ZH1.5-1-GFW13P62	13	18.00	19.90	21.0
C-ZH1.5-1-GFW14P62	14	19.50	21.40	22.5
C-ZH1.5-1-GFW15P62	15	21.00	22.90	24.0
C-ZH1.5-1-GFW16P62	16	22.50	24.40	25.5



TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO. C-ZH1.5-1-GFWNP62	TITLE: ZH1.5 WTB公头胶壳		
X.X±0.20					
X.XX±0.10					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
			SCALE N:A	SHEET 1/2	

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.±0.50	±1°	PART NO.	TITLE:	
X.X±0.20		C-ZH1.5-1-GFWNP62	ZH1.5 WTB公头胶壳	
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		SCALE
MATERILA	---	APPD: Ava		SHEET
FINISH	---			N:A
				2/2