





NOTES:

1. MATERIAL: SEE "TABLE 1";
2. FINISH: SEE "TABLE 1";
3. ELECTRICAL :
 - 3-1.CONTACT CURRENT RATING :DC 30V 0.5A
 - 3-2.INSULATION RESISTANCE : 100 MEGAOHMS MIN.
 - 3-3.DIELECTRIC WITHSTANDING VOLTAGE : 100VAC MIN.
- 4.MECHANICAL CHARACTERISTICS :
 - 4-1. MATING FORCE: 3~20N;
 - 4-2. UNMATING FORCE: 3~20N(INITIAL),2~20N(AFTER 5000 CYCLES);
 - 4-3.DURABILITY : 5,000 MATING CYCLES.
 - 4-4.OPERATING TEMPERATURE : -30°C TO +70°C

TABLE 1:

⑤	弹片端子	1	黄铜	镀亮锡	T=0.15mm
④	弹片端子	1	黄铜	镀亮锡	T=0.15mm
③	弹片端子	1	黄铜	镀亮锡	T=0.15mm
②	弹片端子	1	黄铜	镀亮锡	T=0.15mm
①	主体胶芯	1	PPA	黑色	
NO.	PART NAME	QTY	MATERIAL	DESCRIPTION	REMARK



CIRCUIT DIAGRAM

_____		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME			UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X. 20.25		
			PJ-320A				X.x 20.20		
			HanElectricity Co.,LTD					X.xx 20.15	
							ANGULAIR 73		
FILE.NO.									