






RoHS Compliant




SECTION A-A



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。



序号	品名	材质
①	0.8 Pitch E型 单排侧插BTB母座胶芯	LCP UL94 V-0,颜色:本色
②	0.8 Pitch E型 单排侧插BTB母座端子	铜合金/表面点镀金

Part No	CKT	A	B	C	D
LCK-BTY0851-4PDLYR-GO	2*2	0.80	2.45	3.60	2.60
LCK-BTY0851-6PDLYR-GO	2*3	1.60	3.25	4.40	3.40
LCK-BTY0851-8PDLYR-GO	2*4	2.40	4.05	5.20	4.20
LCK-BTY0851-10PDLYR-GO	2*5	3.20	4.85	6.00	5.00
LCK-BTY0851-12PDLYR-GO	2*6	4.00	5.65	6.80	5.80
LCK-BTY0851-14PDLYR-GO	2*7	4.80	6.45	7.60	6.60
LCK-BTY0851-16PDLYR-GO	2*8	5.60	7.25	8.40	7.40
LCK-BTY0851-18PDLYR-GO	2*9	6.40	8.05	9.20	8.20
LCK-BTY0851-20PDLYR-GO	2*10	7.20	8.85	10.00	9.00
LCK-BTY0851-22PDLYR-GO	2*11	8.00	9.65	10.80	9.80
LCK-BTY0851-24PDLYR-GO	2*12	8.80	10.45	11.60	10.60
LCK-BTY0851-26PDLYR-GO	2*13	9.60	11.25	12.40	11.40
LCK-BTY0851-28PDLYR-GO	2*14	10.40	12.05	13.20	12.20
LCK-BTY0851-30PDLYR-GO	2*15	11.20	12.85	14.00	13.00
LCK-BTY0851-32PDLYR-GO	2*16	12.00	13.65	14.80	13.80
LCK-BTY0851-34PDLYR-GO	2*17	12.80	14.45	15.60	14.60
LCK-BTY0851-36PDLYR-GO	2*18	13.60	15.25	16.40	15.40
LCK-BTY0851-38PDLYR-GO	2*19	14.40	16.05	17.20	16.20
LCK-BTY0851-40PDLYR-GO	2*20	15.20	16.85	18.00	17.00
.....	...	...	...	...	...
LCK-BTY0851-80PDLYR-GO	2*40	31.20	32.85	34.00	33.00

MEASURE POINT:
QUADRANT POINT (QP)
TANGENCY POINT (TP)
INTERSECTION POINT (IP)

UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°



联晟欣连接器(深圳)有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:	0.8 Pitch E型单排侧插BTB母座全规格(标准5.1)
CHECKED		DATE			
APPROVED		DATE			
PART NO: LCK-BTY0851-XXPDLYR-GO	REV: 04	SCALE: 1:1	UNIT: mm		
DRAWING NO: 102022802	SIZE: A4	SHEET: 1/1			