








Kinghelm®



PCB LAYOUT
TOP VIEW (TOLERANCE:±0.05)



SCHEMATIC



技术特性:

使用条件: -30~70°
额定负荷: DC30V 3A
接触电阻: ≤0.03Ω
绝缘电阻: ≥100MΩ DC250V
耐 压: AC500V(50Hz) 1min
插 拔 力: 3~20N
寿 命: 5000次

序号	名 称	数量	材 料	备 注
6	弯 片	1	H62黄铜带(Y) δ=0.30mm	铜锡
5	插 针	1	H62黄铜棒	铜锡
4	后 盖	1	PPA	黑
3	平 片	1	H62黄铜带(Y) δ=0.30mm	铜锡
2	簧 片	1	65Mn 锰钢带 δ=0.20mm	锡铈
1	基 座	1	PA9T	黑

GENERAL TOLERANCES			
0.X	±0.30	X°	±3°
0.XX	±0.20		
0.XXX	±0.10	X.X°	±1°
UNIT	SIZE	SCALE	
MM	A4	1:1	

DRAWN		C	TITLE: 电源插座
DESIGN		PART NO.	DC-013
CHECKED		PRODUCT NO.	KH-DC-013-2.0BCu
APPROVED		DRAWING NO.	
UNIT: mm SCALE: 1:1 RBV: 01-1 SHT: 1 OF 1			

深圳市金航标电子有限公司
www.kinghelm.com.cn
0755-28190160

BCN NO.	RBV	DATE	DESCRIPTION	MDF'D	APP'D
01	2021.12.22	NEW DRAWING RELEASE			