







Kinghelm®



NOTES:

SPECIFICATION:

1. CURRENT RATING: 3A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. INSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 3000 CYCLES

3	SHELL	STAINLESS STEEL	NI/SN Plated	1PCS
2	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

默认公差	图号	客户图	比例	1:1
XX ±0.20	绘图		单位	mm
XX ±0.20	设计		图框	A4
XX ±0.10	审核		页次	1/1
Angle ± 5°	批准		数量	1
尺寸	公差		数量	1

深圳市金航标电子有限公司

www.kinghelm.com.cn

0755-28190160

KH-TYPE-C-16P

Type-c母座板上型(一次成型)