








RoHS Compliant

| 序号 | 品名                          | 材质                    |
|----|-----------------------------|-----------------------|
| ①  | 0.8 Pitch E型<br>单槽侧插BTB公座胶芯 | LCP<br>UL94 V-0,颜色:本色 |
| ②  | 0.8 Pitch E型<br>单槽侧插BTB公座端子 | 铜合金/表面镀金              |



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围:  $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻:  $\leq 0.02\Omega$ 。
5. 绝缘电阻:  $\geq 100\text{M}\Omega$ 。

| Part No                | CKT  | A     | B     | C     | D     |
|------------------------|------|-------|-------|-------|-------|
| LCK-BTG0835-4PDLYR-GO  | 2*2  | 0.80  | 2.35  | 3.35  | 2.60  |
| LCK-BTG0835-6PDLYR-GO  | 2*3  | 1.60  | 3.15  | 4.15  | 3.40  |
| LCK-BTG0835-8PDLYR-GO  | 2*4  | 2.40  | 3.95  | 4.95  | 4.20  |
| LCK-BTG0835-10PDLYR-GO | 2*5  | 3.20  | 4.75  | 5.75  | 5.00  |
| LCK-BTG0835-12PDLYR-GO | 2*6  | 4.00  | 5.55  | 6.55  | 5.80  |
| LCK-BTG0835-14PDLYR-GO | 2*7  | 4.80  | 6.35  | 7.35  | 6.60  |
| LCK-BTG0835-16PDLYR-GO | 2*8  | 5.60  | 7.15  | 8.15  | 7.40  |
| LCK-BTG0835-18PDLYR-GO | 2*9  | 6.40  | 7.95  | 8.95  | 8.20  |
| LCK-BTG0835-20PDLYR-GO | 2*10 | 7.20  | 8.75  | 9.75  | 9.00  |
| LCK-BTG0835-22PDLYR-GO | 2*11 | 8.00  | 9.55  | 10.55 | 9.80  |
| LCK-BTG0835-24PDLYR-GO | 2*12 | 8.80  | 10.35 | 11.35 | 10.60 |
| LCK-BTG0835-26PDLYR-GO | 2*13 | 9.60  | 11.15 | 12.15 | 11.40 |
| LCK-BTG0835-28PDLYR-GO | 2*14 | 10.40 | 11.95 | 12.95 | 12.20 |
| LCK-BTG0835-30PDLYR-GO | 2*15 | 11.20 | 12.75 | 13.75 | 13.00 |
| LCK-BTG0835-32PDLYR-GO | 2*16 | 12.00 | 13.55 | 14.55 | 13.80 |
| LCK-BTG0835-34PDLYR-GO | 2*17 | 12.80 | 14.35 | 15.35 | 14.60 |
| LCK-BTG0835-36PDLYR-GO | 2*18 | 13.60 | 15.15 | 16.15 | 15.40 |
| LCK-BTG0835-38PDLYR-GO | 2*19 | 14.40 | 15.95 | 16.95 | 16.20 |
| LCK-BTG0835-40PDLYR-GO | 2*20 | 15.20 | 16.75 | 17.75 | 17.00 |
| .....                  | ...  | ...   | ...   | ...   | ...   |
| LCK-BTG0835-80PDLYR-GO | 2*40 | 31.20 | 32.75 | 33.75 | 33.00 |

MEASURE POINT:  
QUADRANT POINT (QP)  
TANGENCY POINT (TP)  
INTERSECTION POINT (IP)

UNLESS OTHERWISE  
SPECIFIED, TOLERANCE:  
X.  $\pm 0.25$   
X.x  $\pm 0.20$   
X.xx  $\pm 0.15$   
ANGULAR  $\pm 3^{\circ}$



联晟欣连接器(深圳)有限公司  
Lianshengxin Connector (Shenzhen) Co., Ltd

| DESIGN                          | Andy     | DATE       | 2014.12.24 | TITLE: | 0.8 Pitch E型单槽侧插BTB公座胶芯(料高3.5) |
|---------------------------------|----------|------------|------------|--------|--------------------------------|
| CHECKED                         |          | DATE       |            |        |                                |
| APPROVED                        |          | DATE       |            |        |                                |
| PART NO: LCK-BTG0835-XXPDLYR-GO | REV: 04  | SCALE: 1:1 | UNIT: mm   |        |                                |
| DRAWING NO: 102022802           | SIZE: A4 | SHEET: 1/1 |            |        |                                |