

RoHS Compliant




A

B

C




D

E



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 500\text{M}\Omega$ 。



序号	品名	材质
①	0.8 Pitch F型 单槽立式BTB公座胶芯	PA9T UL94 V-0,颜色:黑色
②	0.8 Pitch F型 单槽立式公座端子	铜合金/表面点镀金

总高(H)	公座单高(H)		母座单高(H)
	H	H1	
4.00	2.80	1.80	2.90
4.50	3.30		
5.00	3.80		
5.50	4.30	2.30	3.40
6.00	4.80		
6.50	5.30		
7.00			3.90

Part No	CKT	A	B	C	D
LCK-BTG0833-6PDLYR-GO	2*3	4.30	2.80	1.60	3.40
LCK-BTG0833-8PDLYR-GO	2*4	5.10	3.60	2.40	4.20
LCK-BTG0833-10PDLYR-GO	2*5	5.90	4.40	3.20	5.00
LCK-BTG0833-12PDLYR-GO	2*6	6.70	5.20	4.00	5.80
LCK-BTG0833-14PDLYR-GO	2*7	7.50	6.00	4.80	6.60
LCK-BTG0833-16PDLYR-GO	2*8	8.30	6.80	5.60	7.40
LCK-BTG0833-18PDLYR-GO	2*9	9.10	7.60	6.40	8.20
LCK-BTG0833-20PDLYR-GO	2*10	9.90	8.40	7.20	9.00
LCK-BTG0833-30PDLYR-GO	2*15	13.90	12.40	11.20	13.00
LCK-BTG0833-40PDLYR-GO	2*20	17.90	16.40	15.20	17.00
LCK-BTG0833-50PDLYR-GO	2*25	21.90	20.40	19.20	21.00
LCK-BTG0833-60PDLYR-GO	2*30	25.90	24.40	23.20	25.00
LCK-BTG0833-70PDLYR-GO	2*35	29.90	28.40	27.20	29.00
LCK-BTG0833-80PDLYR-GO	2*40	33.90	32.40	31.20	33.00
LCK-BTG0833-90PDLYR-GO	2*45	37.90	36.40	35.20	37.00
LCK-BTG0833-100PDLYR-GO	2*50	41.90	40.40	39.20	41.00

MEASURE POINT:
QUADRANT POINT (QP)
TANGENCY POINT (TP)
INTERSECTION POINT (IP)

UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°

联晟欣连接器(深圳)有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN: Andy DATE: 2014.12.24 TITLE:
CHECKED: DATE: 0.8 Pitch F型单槽立式BTB公座业务图(单高3.3)
APPROVED: DATE:
PART NO: LCK-BTG0833-XXPDLYR-GO REV: 04 SCALE: 1:1 UNIT: mm
DRAWING NO: 102022802 SIZE: A4 SHEET: 1/1