







RoHS Compliant



技术指标:

1. 塑件表面应光洁, 无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.1\Omega$.
5. 绝缘电阻: $\geq 500\text{M}\Omega$



序号	品名	材质
①	0.8 Pitch D型 浮动式立式BTB母座浮动胶芯	PA10T UL94 V-0,颜色:黑色
②	0.8 Pitch D型 浮动式立式BTB母座底座	PA10T UL94 V-0,颜色:黑色
③	0.8 Pitch D型 浮动式立式BTB母座端子	铜合金/表面镀金
④	0.8 Pitch D型 浮动式立式BTB母座弹片	铜合金/表面镀锡
⑤	0.8 Pitch D型 浮动式立式BTB母座胶盖	LCP 130i UL94 V-0,颜色:黑色

0.8 浮动式 SMT 板对板合高配合情况

合高 母座单高	公座单高	4.8	6.8
8.5	9.75	11.75	

浮动式板对板支持X.Y.Z三方向±0.5的摆动

Part No	CKT	A	B	C	D	E	F
LCK-BTY0885-30PDLYC-GO	2X15	11.20	12.90	14.4600	21.00	18.00	21.00
LCK-BTY0885-40PDLYC-GO	2X20	15.20	16.90	18.4600	25.00	22.00	25.00
LCK-BTY0885-50PDLYC-GO	2X25	19.20	20.90	22.4600	29.00	26.00	29.00
LCK-BTY0885-60PDLYC-GO	2X30	23.20	24.90	26.4600	33.00	30.00	33.00
LCK-BTY0885-70PDLYC-GO	2X35	27.20	28.90	30.4600	37.00	34.00	37.00
LCK-BTY0885-80PDLYC-GO	2X40	31.20	32.90	34.4600	41.00	38.00	41.00
LCK-BTY0885-90PDLYC-GO	2X45	35.20	36.90	38.4600	45.00	42.00	45.00
LCK-BTY0885-100PDLYC-GO	2X50	39.20	40.90	42.4600	49.00	46.00	49.00
LCK-BTY0885-110PDLYC-GO	2X55	43.20	44.90	46.4600	53.00	50.00	53.00
LCK-BTY0885-120PDLYC-GO	2X60	47.20	48.90	50.4600	57.00	54.00	57.00

MEASURE POINT:
QUADRANT POINT (QP)
TANGENCY POINT (TP)
INTERSECTION POINT (IP)

UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°



联晟欣连接器 (深圳) 有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:	0.8 Pitch D型浮动式立式BTB母座底壳(半高8.5)
CHECKED		DATE			
APPROVED		DATE			
PART NO: LCK-BTY0885-XXPDLYC-GO	REV: 04	SCALE: 1:1	UNIT: mm		
DRAWING NO: 102022802	SIZE: A4	SHEET: 1/1			