

RoHS Compliant


A

B

C






D

E



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 1000\text{M}\Omega$ 。



序号	品名	材质
①	0.8 Pitch F型 单槽立式BTB母座胶芯	PA9T UL94 V-0,颜色:黑色
②	0.8 Pitch F型 单槽立式母座端子	铜合金/表面点镀金
③	0.8 Pitch B型 单槽立式BTB麦拉	耐高温不干胶

总高(H)	公座单高(H1)	母座单高(H2)
4.00	2.80	2.90
4.50	3.30	
5.00	3.80	
5.50	4.30	3.40
6.00	4.80	
6.50	5.30	
7.00		3.90

Part No	CKT	A	B	C	D
LCK-BTY0829-6PDLYR-GO	2*3	4.30	2.80	1.60	3.40
LCK-BTY0829-8PDLYR-GO	2*4	5.10	3.60	2.40	4.20
LCK-BTY0829-10PDLYR-GO	2*5	5.90	4.40	3.20	5.00
LCK-BTY0829-12PDLYR-GO	2*6	6.70	5.20	4.00	5.80
LCK-BTY0829-14PDLYR-GO	2*7	7.50	6.00	4.80	6.60
LCK-BTY0829-16PDLYR-GO	2*8	8.30	6.80	5.60	7.40
LCK-BTY0829-18PDLYR-GO	2*9	9.10	7.60	6.40	8.20
LCK-BTY0829-20PDLYR-GO	2*10	9.90	8.40	7.20	9.00
LCK-BTY0829-30PDLYR-GO	2*15	13.90	12.40	11.20	13.00
LCK-BTY0829-40PDLYR-GO	2*20	17.90	16.40	15.20	17.00
LCK-BTY0829-50PDLYR-GO	2*25	21.90	20.40	19.20	21.00
LCK-BTY0829-60PDLYR-GO	2*30	25.90	24.40	23.20	25.00
LCK-BTY0829-70PDLYR-GO	2*35	29.90	28.40	27.20	29.00
LCK-BTY0829-80PDLYR-GO	2*40	33.90	32.40	31.20	33.00
LCK-BTY0829-90PDLYR-GO	2*45	37.90	36.40	35.20	37.00
LCK-BTY0829-100PDLYR-GO	2*50	41.90	40.40	39.20	41.00

MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)	DESIGN CHECKED APPROVED	Andy DATE DATE	DATE 2014.12.24	TITLE: 0.8 Pitch F型单槽立式BTB母座麦拉(单高2.9)
UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°	PART NO: LCK-BTY0829-XXPDLYR-GO DRAWING NO: 102022802	REV: 04 SCALE: 1:1 UNIT: mm	SIZE: A4 SHEET: 1/1	

A

B

C

D

E