





Kinghelm®

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A0.	/	New Edition Release	2026.04.27	



PCB LAYOUT

Materials and Electroplating

- ①. Plastic body: PA66, UL94V-0
- ②. Solder pin: copper, Nickel tin plating

Electrical performance

Rated voltage: 300V
Rated current: 8A
Contact resistance: 20m Ω (Max)
Insulation resistance: 500M Ω \ DC500V
Voltage endurance: AC1500V \ 1Min

mechanical properties

Temperature range: -40 ℃~+105 ℃
Instantaneous temperature: +250 ℃, 5 seconds

深圳市金航标电子有限公司

www.kinghelm.com.cn

0755-28190160

公差参数

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.20
7-12P		±0.20	±0.30
13-18P		±0.25	±0.40
19-24P		±0.30	±0.50

X.X ±0.35
X.XX ±0.25
X.XXX ±0.15

NAME:

3.81 接线端子 弯针 系列

P/N: KH-15EDGRC-3.81-***PG-1
(**代表P数)

DWG NO:

THIRD ANGLE PROJECTION



DRAWN:

UNIT:	SCALE	SIZE:	SHEET:	REV.
MM	1:1	A4	1/1	A0

CHECKED:

APPROVED: