

RoHS

REV.

ECN.#

DESCRIPTION

NAME


DATE

A0


NEW RELEASE

HZP






2023.01.02



P/N	MID.A	MID.B
2P	2.00	8.00
3P	4.00	10.00
4P	6.00	12.00
5P	8.00	14.00
6P	10.00	16.00



RECOMMENDED PCB LAYOUT
TOLERANCE=±0.05



WITH CAP VIEW
SCALE 1:2

Specifications:

- 1.Rated Voltage :125V AC/DC
- 2.Rated Current :1A AC/DC
- 3.Withstand Voltage :200V AC/minute
- 4.Contact Resistance:50mΩ (MAX.)
- 5.Insulation Resistance :100mΩ (MIN.)
- 6.Storage Temperature Range: -40℃~+85℃;
- 7.Operation Temperature Range: -25℃~+70℃;

③	端子	黄铜	镀锡
②	固定片	黄铜	镀锡
①	塑胶主体	LCP	本色
序号	配件名称	材质	电镀 颜色

MILLIMETERS	INCH
X.* ±2*	X.* ±2*
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF DongGuan JinBilal
Metal Plastic Technology Co.,Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE
PRIOR WRITTEN CONSENT OF DongGuan
JinBilal Metal Plastic Technology Co.,Ltd




东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	Wafer 2.0Pitch 立贴加盖	DR		
PART NO.	108501052-XX	CHKD		
PRO J.	PAGE 1/1	UNITS mm	APPD	
SIZE	A4	SCALE 1:1	DIS NO.	

RoHS

USER DIRECTION OF UNREELING


COVER TAPE PEELING ANGLE: $165^\circ \sim 180^\circ$

PEELING FORCE: 20~130g

CARRIER TAPE


USER DIRECTION OF UNREELING

DETAIL B




NOTES

1. NUMBER OF CONNECTORS: 700PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 6300PCS/CARTON



MILLIMETERS	INCH	 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X.* $\pm 2^\circ$	X.* $\pm 2^\circ$	TITLE	Wafer 2.0Pitch 立贴加盖	DR	
.X ± 0.30	.X ± 0.012	PART NO.	108501052-XX	CHKD	
.XX ± 0.20	.XX ± 0.008	PRO J.	PAGE 2/2	UNITS mm	APPD
.XXX ± 0.10	.XXX ± 0.004	SIZE	A4	SCALE 1:1	DIS NO.
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd					