

RoHS

REV.

ECN.#

DESCRIPTION

NAME


DATE

A0

NEW RELEASE




HZP

2023.01.02



2P

3P





Specifications:

- 1.Rated Voltage :125V AC/DC
- 2.Rated Current :1A AC/DC
- 3.Withstand Voltage :200V AC/minute
- 4.Contact Resistance:50mΩ (MAX.)
- 5.Insulation Resistance :100mΩ (MIN.)
- 6.Storage Temperature Range:-40℃~+85℃;
- 7.Operation Temperature Range:-25℃~+70℃;

P/N	MID.A	MID.B
2P	1.25	7.50
3P	2.50	8.75
4P	3.75	10.00
5P	5.00	11.25
6P	6.25	12.50
7P	7.50	13.75
8P	8.75	15.00

③	端子	黄铜	镀锡
②	固定片	黄铜	镀锡
①	塑胶主体	LCP	本色
序号	配件名称	材质	电镀 颜色



MILLIMETERS	INCH
X.* ±2*	X.* ±2*
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBilal Metal Plastic Technology Co.,Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBilal Metal Plastic Technology Co.,Ltd



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	Wafer 1.25Pitch 立贴加盖	DR		
PART NO.	108501062-XX	CHKD		
PRO J.	PAGE 1/1	UNITS mm	APPD	
SIZE	A4	SCALE 1:1	DIS NO.	