









06~15P SHAPE
SCALE 1:1



02~03P SHAPE
SCALE 1:1



04~05P SHAPE
SCALE 1:1

- NOTE:
1. MATERIAL: P466, NATURAL COLOR, HALOGEN FREE, UL94V-0
 2. MATE WITH AFCI 101565053 & 10155054
 3. USE WITH AFCI 10166892 CRIMP TERMINAL
 4. PRODUCT SPEC: GS-12-1566
 5. ORDERING CODE: 10155056-XX 0 X LF

NUMBER OF PINS ———
02~15: 02~15PINS
BLANK: STANDARD
G: CUSTOMER CODE
PACKAGE
1: BAG

POS	DIMENSIONS(MM)		
	A	B	C
02	1.50	7.30	4.25
03	3.00	8.80	5.75
04	4.50	10.30	7.25
05	6.00	11.80	8.75
06	7.50	13.30	10.25
07	9.00	14.80	11.75
08	10.50	16.30	13.25
09	12.00	17.80	14.75
10	13.50	19.30	16.25
11	15.00	20.80	17.75
12	16.50	22.30	19.25
13	18.00	23.80	20.75
14	19.50	25.30	22.25
15	21.00	26.80	23.75

mat'l. code		surface		tolerance		projection		product family	
ISO 1302		ISO 406		ISO 1101		FitMate			
tr	ecn no	dr	date	tolerances unless otherwise specified	linear	mm	mm	title	sheet 1 of 1
A	New Release	Jason	2020/4/20	angles	XX±.20	—	—	1.5mm Pitch RECEPTACLE HOUSING	size
B	EX-N-55541	CP	JF2025/04/22	linear	XXX±.10	—	—		A3
C	EX-N-55900	CP	JF2025/05/28	dr	Jason Wang	2019-10-08	—		
				eng	Jason Wang	2020-4-20	—		
				chr	—	—	—		
				oppd	Tim Yoo	2020-4-20	—		
sheet	revision	C							
index	sheet	1							