



RoHS





REV.	ECN.#	DESCRIPTION	NAME	DATE
A0		NEW RELEASE	HZP	2023.01.02



P/N	MID.A	MID.B
2P	8.00	2.00
3P	10.00	4.00
4P	12.00	6.00
5P	14.00	8.00
6P	16.00	10.00



RECOMMENDED PCB LAYOUT
TOLERANCE=±0.05



- Specifications:
- 1.Rated Voltage :125V AC/DC
 - 2.Rated Current :1A AC/DC
 - 3.Withstand Voltage :200V AC/minute
 - 4.Contact Resistance:50mΩ (MAX.)
 - 5.Insulation Resistance :100mΩ (MIN.)
 - 6.Storage Temperature Range :−40℃~+85℃;
 - 7.Operation Temperature Range :−25℃~+70℃;

③	端子	黄铜	镀锡
②	固定片	黄铜	镀锡
①	塑胶主体	LCP	本色
序号	配件名称	材质	电镀 颜色

MILLIMETERS		INCH		 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X.* ±2*	X.* ±2*	X.* ±2*	X.* ±2*				
.X ±0.30	.X ±0.12	.X ±0.12	.X ±0.12				
.XX ±0.20	.XX ±0.008	.XX ±0.008	.XX ±0.008				
.XXX ±0.10	.XXX ±0.004	.XXX ±0.004	.XXX ±0.004				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd				TITLE	Wafer 2.0 Pitch 卧贴	DR	
				PART NO.	108501082-XX	CHKD	
				PRO J.	PAGE 1/1	UNITS mm	APPD
				SIZE	A4	SCALE 1:1	DIS NO.