

RoHS

REV.

ECN.#

DESCRIPTION

NAME


DATE

A0


NEW RELEASE

HZP





2023.01.02



P/N	MID.A	MID.B
2P	1.50	6.00
3P	3.00	7.50
4P	4.50	9.00
5P	6.00	10.50



RECOMMENDED PCB LAYOUT
TOLERANCE=±0.05



Specifications:

- 1.Rated Voltage :125V AC/DC
- 2.Rated Current :1A AC/DC
- 3.Withstand Voltage :200V AC/minute
- 4.Contact Resistance:50mΩ (MAX.)
- 5.Insulation Resistance :100mΩ (MIN.)
- 6.Storage Temperature Range: -40℃~+85℃;
- 7.Operation Temperature Range: -25℃~+70℃;

③	端子	黄铜	镀锡
②	固定片	黄铜	镀锡
①	塑胶主体	LCP	本色
序号	配件名称	材质	电镀 颜色

MILLIMETERS	INCH
X.* ±2*	X.* ±2*
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd	



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	Wafer 1.5 Pitch 贴片	DR		
PART NO.	108501092-XX	CHKD		
PRO J.	PAGE 1/1	UNITS mm	APPD	
SIZE	A4	SCALE 1:1	DIS NO.	