





CIRCUIT DIAGRAM



TECHNICAL PARAMETERS
1.RATED CURRENT: 50MA AT 12V DC
2.CONTACT RESISTANCE: 100 MΩ (MILLIOHMS)
3.TRAVEL: 0.2±0.1 MM
4.INSULATION RESISTANCE: 100 MΩ (MEGOHMS) MIN.
5.WITHSTANDING VOLTAGE: 250V AC, 50HZ, FOR 1 MINUTE

E	COVER PLATE	1	BRASS	COPPER-TIN PLATED	
D	PUSH BUTTON	1	LCP	WHITE	
C	CONTACT SPRING	1	SUS		
B	BASE HOUSING	1	PPA	CLEANED	
A	RETAINER CLIP	1	BRASS	Ag PLATING	
NO	NAME	NUMBER	MATERIAL	ELECTRIC PLATING	REMARKS

SHENZHEN FUGANG TECHNOLOGY CO.,LTD					
DSND	H	J	2026.03.28	TITLE:TACT SWITCH	
CHKD	Y	H	C	2026.03.28	PART NO:TC-3603C-H-XXX
APVD	L	P	J	2026.03.28	
UNIT:mm		SCALE:1:1		SIZE:A4	SHEET:1/1



PART NO:TC-3603C-H-XXX
H=2.5 160--160gf
H=3.0 260--260gf

PCB HOLES(TOP VIEW)
GENERAL TOLERANCE:±0.05mm

按力	160±30gf	260±50gf
寿命	3万次	3万次

TOLERANCE UNLESS OTHERWISE SPEC	
BASIC DIMENSION	TOLERANCE
>0.5-2	±0.1
>2-5	±0.20
>5以上	±0.30
ANGLES	±1°