




REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		初版发行				
		XHB-2A	7.50mm	6.10mm	2.50mm	2.50mm
		XHB-3A	10.00mm	8.60mm	5.00mm	2.50mm
		XHB-4A	12.50mm	11.10mm	7.50mm	3.60mm
		XHB-5A	15.00mm	13.60mm	10.00mm	6.00mm
		XHB-6A	17.50mm	16.10mm	12.50mm	8.80mm
		XHB-7A	20.00mm	18.60mm	15.00mm	11.20mm
		XHB-8A	22.50mm	21.10mm	17.50mm	13.80mm
		XHB-9A	25.00mm	23.60mm	20.00mm	16.20mm
		XHB-10A	27.50mm	26.10mm	22.50mm	18.80mm
		XHB-11A	30.00mm	28.60mm	25.00mm	21.20mm
		XHB-12A	32.50mm	31.10mm	27.50mm	23.80mm
		XHB-13A	35.00mm	33.60mm	30.00mm	26.20mm
		XHB-14A	37.50mm	36.10mm	32.50mm	28.80mm
		XHB-15A	40.00mm	38.60mm	35.00mm	31.20mm
		XHB-16A	42.50mm	41.10mm	37.50mm	34.00mm
		CKT	DIM.A	DIM.B	DIM.C	DIM.D

PCB LAYOUT

技术参数Technical Index			
温度范围Temperature range:	-25℃~85℃	耐压值Withstanding voltage:	800V AC/minute
额定电压Voltage rating:	250V AC/DC	适用线规 Apply to gauge	AWG28#~22#
额定电流Current rating	3A AC/DC		
接触电阻Contact resistance:	≤0.01Ω		
绝缘电阻resistance:	≥1000MΩ		

GENERAL TOLERANCES			
DIM	TOL	DIM	DEG
X		X°	±3.00°
X.X	±0.35	X.X°	±2.00°
X.XX	±0.25	X.XX°	±1.00°
X.XXX	±0.15	X.XXX°	

2	PIN	N PCS	铜合金/表面镀高温锡: Copper Alloy/Tin Plating
1	Housing	1 PCS	PA66 OR 增强PA66(UL94-V0), 黑色 Notural
No.	NAME	Q'TY	DESCRIPTION

 韩下® HANXIA 深圳市韩下电子有限公司			
DRAW :	黄彬	2023.9.18	TITLE: 针座
DESIGN:			DRAW NAME: HX-XHB2.54-3PZZ-B
CHECK:	张伟	2023.9.18	
APPROVED	罗小春	2023.9.18	SERIES: 2.5 SERIES
CUSTOMER DRAWING		P/N: NX-A25002-A	DRAW NO.
		REV. 1.00	UNIT: mm
		SCALE N/A	SHEET: 1/1
			