




REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		初版发行				
		XHB-2AW	7.50mm	6.10mm	2.50mm	2.50mm
		XHB-3AW	10.00mm	8.60mm	5.00mm	2.50mm
		XHB-4AW	12.50mm	11.10mm	7.50mm	3.60mm
		XHB-5AW	15.00mm	13.60mm	10.00mm	6.00mm
		XHB-6AW	17.50mm	16.10mm	12.50mm	8.80mm
		XHB-7AW	20.00mm	18.60mm	15.00mm	11.20mm
		XHB-8AW	22.50mm	21.10mm	17.50mm	13.80mm
		XHB-9AW	25.00mm	23.60mm	20.00mm	16.20mm
		XHB-10AW	27.50mm	26.10mm	22.50mm	18.80mm
		XHB-11AW	30.00mm	28.60mm	25.00mm	21.20mm
		XHB-12AW	32.50mm	31.10mm	27.50mm	23.80mm
		XHB-13AW	35.00mm	33.60mm	30.00mm	26.20mm
		XHB-14AW	37.50mm	36.10mm	32.50mm	28.80mm
		XHB-15AW	40.00mm	38.60mm	35.00mm	31.20mm
		XHB-16AW	42.50mm	41.10mm	37.50mm	34.00mm
		CKT	DIM.A	DIM.B	DIM.C	DIM.D



2-6PIN连扣

7PIN以上断扣

PCB LAYOUT

技术参数Technical Index

温度范围Temperature range:	-25℃~85℃	耐压值Withstanding voltage:	800V AC/minute
额定电压Voltage rating:	250V AC/DC	适用线规 Apply to gauge	AWG28#~22#
额定电流Current rating	3A AC/DC		
接触电阻Contact resistance:	≤0.01Ω		
绝缘电阻resistance:	≥1000MΩ		

GENERAL TOLERANCES

DIM	TOL	DIM	DEG
X		X°	±3.00°
X.X	±0.35	X.X°	±2.00°
X.XX	±0.25	X.XX°	±1.00°
X.XXX	±0.15	X.XXX°	

2	PIN	N PCS	铜合金/表面镀高温锡: Copper Alloy/Tin Plating
1	Housing	1 PCS	PA66 OR 增强PA66(UL94-V0), 本色 Notural
No.	NAME	Q'TY	DESCRIPTION



深圳市韩下电子有限公司

DRAW:	黄彬	TITLE:	针座	DRAW NAME:	
DESIGN:		SERIES:	2.5 SERIES		
CHECK:	张伟	P/N:	NX-A25002-AW	DRAW NO.	
APPROVED	罗小春	REV.	1.00	SCALE	N/A
CUSTOMER DRAWING			UNIT:	SHEET:	
			mm	1/1	