



规格 PTF-76
文件号 A-2026-PTF-76-G
版本1
Shape and Size (mm)


Structure	Material	Marked
Shell	PA66	UL 94 V0
Pin	Tin Plated Brass/Nickel Plated Brass	-

Electrical Performance

Model	For Fuse	Rated Ampere	Rated Voltage	Operating Power	Insulation Resistance	Di-electronic Strength
PTF-76	5*20mm	10A	250V	1.6W	>100MΩ	>500Vac/60'

Package and Assembly

Model	Qty	Wave Soldering	Hand Soldering
PTF-76	500Pcs/Bag	260℃ Max	350℃ 5 seconds max

Storage and Expiration date

- Storage conditions: Package need to be sealed completely, temperature 25℃ (+5℃, -10℃)、relative humidity 40%RH(+30%RH, -20%RH).
- Expiration date : For packing products : 6 months , For unpacking products : recommend one week. Due to the risk of oxidation for unpacking product, please seal completely the package for the remainders.