

SECTION A-A

SECTION B-B

SECTION C-C

3D VIEW

NOTES:

- 1.MATERIAL: P-PHOSPHOR BRONZE, T=0.15mm
 - 2.INSULATION O.D.:1.28mm(MAX)
WIRE RANGE: AWG#24; AWG#25; AWG#26
 - 3.MATES WITH HOUSING: 10155056 & 10166893
 - 4.ROHS STANDARD SPECIFICATION ACCORDING TO FCI GS-22-008
 - 5.ORDERING CODE:10166892-1 X LF
- LEAD FREE
Plating :
0:Bright tin
1:30u" Gold ON CONTACT AREA

mat'l. code				surface	tolerance	projection	product family			
				ISO 1302	ISO 406 ISO 1101		FitMate			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title			
A	New Release	CP Ji	2025/04/28	angles	.X±.3		1.50mm pitch connector terminal			
				linear	.XX±.20					
				0'±x'	.XXX±.10	scale 6:1				
				dr	Tian Le Wang 2022-3-23	Amphenol FCI	dwg no		sheet 1 of 1	size
				eng	Tian Le Wang 2022-3-23		10166892			A3
				chr	Song Yang 2022-3-23					
				appd	TIM YAO 2022-3-23		type Product Customer Drawing			
sheet index	revision	A								
	sheet	1								