





Ordering Information

Temperture Range: -40° C to+105° C



P220-22 XX A0 C S 170 B 1

HEIGHT OF HOUSING
10:1.0mm
15:1.5mm
20:2.0mm

NO.OF PIN
PER ROW

Full Of Gold

Semi-gold

INSULATOR LENGTH
MATERIAL: OF
B:PA6T TERMINAL
C:PA9T
D:LCP

PACKING
A:PE Bag
B:Tape & Reel
C:Tube
D:Tube+CAP
E:Tray

$$\begin{aligned} A_0 &= 0.8u'' \\ A_1 &= 1u'' \\ A_2 &= 1.5u'' \end{aligned}$$

A3=2u"	B3=2U"
A4=3u"	B4=3U"
A5=5u"	B5=5U"

A3=3u	B3=3u
A6=10u"	B6=10U"
A7=15u"	B7=15U"

A8=20u" B8=20U"
A9=30u" B9=30U"
S1=Ordinary Tip Plated

S1=Ordinary Tin Plated
S2=Matte Tin Plated
S3=Tin-plated High-temperature

S4=High Temperture Matt Tin

				OPERATION		SCALE		Fit	 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM			
				X.XX	±0.20	SIZE	A4	DESIGN	李青杰2023.06.14	PART NO.	P220-22XXA0CS170B1
				X.XXX	±0.10						
				Angle	±3°	SHEET	1/1	CHECK		TITLE:	PH2.0 2*8P*2 L=17.0/3.0/3.0 180度 PA9T 镀金足0.8U"镍底足30U" CAP+150PCS/卷 V1195
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DWG	TOL	PROJ		APPROVE		Customer No.	