

Specifications

备注(Remark)

1. 材料(MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing:PA9T+30%G.F UL94V-0, Color:Black

四方针：黄铜，镍底30u"MIN, 表面镀金0.8u"MIN

Contact: Brass, 0.8u" MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Raring Current:3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.





Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage:AC 500V/Minute.

温度范围: -40°C to $+105^{\circ}\text{C}$

Temperture Range: -40° C to+105° C



Ordering Information
P125-32 03 A0 C S 392 A 1

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact	Plating	INSULATOR MATERIAL	LENGTH OF	PACKING
15:1.5mm	2-40P	Full Of Gold	Semi-gold	A:PBT	TERMINAL	A:PE Bag B:Tape & Reel
17:1.7mm		A0=0.8u"	B0=0.8u"			
20:2.0mm		A1=1u"	B1=1u"	B:PA6T		C:Tube
25:2.54mm		A2=1.5u"	B2=1.5u"	C:PA9T		D:Tube+CAP
30:3.0mm		A3=2u"	B3=2u"	D:LCP		E:Tray
		A4=3u"	B4=3u"			
		A5=5u"	B5=5u"			
		A6=10u"	B6=10u"			
		A7=15u"	B7=15u"			
		A8=20u"	B8=20u"			
		A9=30u"	B9=30u"			
		S1=Ordinary Tin Plated				
		S2=Matte Tin Plated				
		S3=Tin-plated High-temperature				

				OPERATION		SCALE		Fit	 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM			
				X.XX	±0.20	SIZE	A4	DESIGN	秦星宇 2020.09.29	PART NO.	P125-3203A0CS392A1
				X.XXX	±0.10						
				Angle	±3°	SHEET	1/1	CHECK		TITLE:	PH2.54 2*3P*3 L=39.2/2.5/9.6 180度 PA9T料 镀普金 500PCS/袋 K5005
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.	