

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G. F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G. F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u"MIN, 表面镀金足1u"MIN

Contact: Brass, 1u"MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Raring Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.





Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Ordering Information

P125-12 03 A1 C S 116 A 1

HEIGHT OF HOUSING	NO.OF PINS PER ROW	Contact Plating	INSULATOR MATERIAL:	LENGTH OF TERMINAL	PACKING
15:1.5mm	2~40P	Full Of Gold	A: PBT		A: PE Bag
17:1.7mm		A0=0.8u"	B: PA6T		B: Tape & Reel
20:2.0mm		A1=1u"	C: PA9T		C: Tube
25:2.5mm		A2=1.5u"	D: LCP		D: Tube+CAP
30:3.0mm		A3=2u"			E: Tray
		A4=3u"			
		A5=5u"			
		A6=10u"			
		A7=15u"			
		A8=20u"			
		A9=30u"			
		S1=Ordinary Tin Plated			
		S2=Matte Tin Plated			
		S3=Tin-plated High-temperature			

				OPERATION		SCALE		Fit	Yxcon 东莞市宇熙精密连接器有限公司			
				X.X	±0.25	UNIT		MM	www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.			
				X.XX	±0.20	SIZE	A4	DESIGN	李官淼2022.05.28	PART NO.	P125-1203A1CS116A1	
				X.XXX	±0.10	SHEET		1/1	CHECK		2.54排针 2*3P 1=11.6/3.0 180度	
				Angle	±3°	PROJ.		APPROVE		TITLE:	PA9T料 镀金足1u" 袋装 K6063	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL					Customer No.		