




Ordering Information

Temperture Range: -40° C to $+105^{\circ}\text{ C}$



HEIGHT OF HOUSING	NO.OF PINS PER ROW	Contact Plating Full Of Gold	INSULATOR OF	LENGTH OF	PACKING
15:1.5mm	2~40P	A0=0.8u"	A:PBT	TERMINAL	A:PE Bag B:Tape & Reel
17:1.7mm		A1=1u"	B:PA6T		C:Tube
20:2.0mm		A2=1.5u"	C:PA9T		D:Tube+CAP
25:2.54mm		A3=2u"	D:LCP		E:Tray
30:3.0mm		A4=3u"			
		A5=5u"			
		A6=10u"			
		A7=15u"			
		A8=20u"			
		A9=30u"			
		S1=Ordinary Tin Plated			
		S2=Matte Tin Plated			
		S3=Tin-plated High-temperature			

				OPERATION		SCALE		Fit	 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.20	UNIT		MM			
				X.XX	±0.15	SIZE	A4	DESIGN	李官淼2022. 12. 09	PART NO.	P220-11XXA0CR105A1
				X.XXX	±0.08						
				Angle	±2°	SHEET	1/1	CHECK		TITLE:	2. 0排针 1*3P L=10. 5/2. 8/4. 0(0. 75) 90度 打内K 1R前1. 0kg后0. 6 成型P 弯平面 PA9T 镀金足0. 6U镍30U 盐雾24H 袋装 K2001
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.	