

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u"MIN, 表面镀金0.8u"MIN

Contact: Brass, 0.8u"MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Rating Current: 2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.




Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V.

Withstanding Voltage: AC 500V.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Ordering Information

P220-11 03 A0 C R 140 A 1

HEIGHT OF HOUSING	NO.OF PINS PER ROW	Contact Plating Full Of Gold	Semi-gold	INSULATOR MATERIAL:	LENGTH OF TERMINAL	PACKING
10:1.0mm	1~40P	A0=0.8u"	B0=0.8U"	B:PA6T		A:PE Bag
15:1.5mm		A1=1u"	B1=1U"	C:PA9T		B:Tape & Reel
20:2.0mm		A2=1.5u"	B2=1.5U"	D:LCP		C:Tube
		A3=2u"	B3=2U"			D:Tube+CAP
		A4=3u"	B4=3U"			E:Tray
		A5=5u"	B5=5U"			
		A6=10u"	B6=10U"			
		A7=15u"	B7=15U"			
		A8=20u"	B8=20U"			
		A9=30u"	B9=30U"			
		S1=Ordinary Tin Plated				
		S2=Matte Tin Plated				
		S3=Tin-plated High-temperature				

					OPERATION		SCALE		Fit				
--	--	--	--	--	-----------	--	-------	--	-----	--	--	--	--