

Ordering Information

备注(Remark)

1. 材料(MATERIAL)

胶芯: PBT+30%G.F UL94V-0, 颜色: 黑色.

Housing:PBT+30%G.F UL94V-0, Color:Black

四方针：黄铜，镍底30u"MIN, 表面镀金3u"MIN

Contact: Brass, 3u" MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Raring Current:3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.





Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage:AC 500V/Minute.

温度范围: -40°C to $+105^{\circ}\text{C}$

Temperture Range: -40° C to+105° C



HEIGHT OF HOUSING	NO.OF PINS PER ROW	Contact Plating		INSULATOR MATERIAL:	LENGTH OF	PACKING
15:1.5mm	1~40P	Full Of Gold	Semi-gold	A:PA9T		A:PE Bag
17:1.7mm		A1=1u"	B1=1U"	B:PA6T		C:Tube
20:2.0mm		A2=1.5u"	B2=1.5U"	C:PBT		D:Tube+CAP
25:2.54mm		A3=2u"	B3=2U"	D:LCP		E:Tray
		A4=3u"	B4=3U"			
		A5=5u"	B5=5U"			
		A6=10u"	B6=10U"			
		A7=15u"	B7=15U"			
		A8=20u"	B8=20U"			
		A9=30u"	B9=30U"			
		S1=Ordinary Tin Plated				
		S2=Matte Tin Plated				
		S3=Tin-plated High-temperature				

				OPERATION		SCALE		Fit	东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM			
				X.XX	±0.20	SIZE	A4	DESIGN	李官淼2022.05.04	PART NO.	P125-1114A4AS150A1
				X.XXX	±0.10						
				Angle	±3°	SHEET	1/1	CHECK		TITLE:	2.54排针 1*14P L=15.0/3.0 180度 PBT 镀3u"金 500个/袋
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.	