

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u"MIN, 表面镀金1u"MIN

Contact: Brass, 1u"MIN GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.





Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperature Range: -40° C to +105° C



Ordering Information

P125-11 22 A1 A S 135 A 1

HEIGHT OF HOUSING	NO.OF PINS PER ROW	Contact Plating		INSULATOR MATERIAL:	LENGTH OF TERMINAL	PACKING
15:1.5mm	1~40P	Full Of Gold	Semi-gold	A: PBT		A: PE Bag
17:1.7mm		A0=0.8u"	B0=0.8U"	B: PA6T		B: Tape & Reel
20:2.0mm		A1=1u"	B1=1U"	C: PA9T		C: Tube
25:2.54mm		A2=1.5u"	B2=1.5U"	D: LCP		D: Tube+CAP
		A3=2u"	B3=2U"			E: Tray
		A4=3u"	B4=3U"			
		A5=5u"	B5=5U"			
		A6=10u"	B6=10U"			
		A7=15u"	B7=15U"			
		A8=20u"	B8=20U"			
		A9=30u"	B9=30U"			
		S1=Ordinary Tin Plated				
		S2=Matte Tin Plated				
		S3=Tin-plated High-temperature				

OPERATION

SCALE

Fit

X.X ±0.25

UNIT

MM

X.XX ±0.20

SIZE

A4

DESIGN

刘伟 2021.07.28

PART NO.

P125-1122A1AS135A1

X.XXX ±0.10

SHEET

1/1

CHECK

TITLE:

2.54排针 1*22P L=13.5/3.0 180度

PA9T 镀10金 200/袋

Angle ±3°

DIM TOL

PROJ.

APPROVE

Customer No.

MODIFICATION DESCRIPTION

Yxcon

www.yxcon.com

东莞市宇熙精密连接器有限公司

Dongguan Yuxi Electronic Co.,Ltd.