




Specifications

备注 (Remark)
1. 材料 (MATERIAL)
胶芯: PBT+30%G. F UL94V-0, 颜色: 黑色.
Housing: PBT+30%G. F UL94V-0, Color: Black
四方针: 黄铜, 镍底, 表面镀普金
Contact: Brass, GOLD PLATING OVER ALL
NICKEL UNDERPLATING OVER ALL


2. 特性 (characteristics):
额定电流: 3 AMP
Raring Current: 3 AMP.
接触阻抗: 20 mΩ MAX.
Contact Resistance: 20 mΩ MAX.
绝缘阻抗: 1000 MΩ MIN.
Insulating Resistance: 1000 MΩ MIN.
耐电压: AC 500V/分钟.
Withstanding Voltage: AC 500V/Minute.
温度范围: -40° C to +105° C
Temperture Range: -40° C to +105° C



Ordering Information

P125-12 06 A0 A S 116 A 5

HEIGHT OF HOUSING	NO.OF PINS PER ROW	Contact Plating	INSULATOR MATERIAL:	LENGTH OF TERMINAL	PACKING
15:1.5mm	2~40P	Full Of Gold	A: PBT		A: PE Bag
17:1.7mm		A0=G/F"	B: PA6T		B: Tape & Reel
20:2.0mm		A1=1u"	C: PA9T		C: Tube
25:2.54mm		A2=1.5u"	D: LCP		D: Tube+CAP
30:3.0mm		A3=2u"			E: Tray
		A4=3u"			
		A5=5u"			
		A6=10u"			
		A7=15u"			
		A8=20u"			
		A9=30u"			
		S1=Ordinary Tin Plated			
		S2=Matte Tin Plated			
		S3=Tin-plated High-temperature			



				OPERATION		SCALE		Fit	Yxcon 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM			
				X.XX	±0.20	SIZE	A4	DESIGN	罗康 2026. 10. 09	PART NO.	P125-1206A0AS116A5
				X.XXX	±0.10						
				Angle	±3°	SHEET	1/1	CHECK		TITLE:	2.54排针 2*6P L=11.6/3.0 180度 加白点 打内K 第3.4P L=12.0/3.0 PBT料 镀普金 1K/袋
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.	