

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u"MIN, 表面镀普金

Contact: Brass, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 1 AMP

Raring Current: 1 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.




Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C


Temperture Range: -40° C to +105° C



Ordering Information

P320-22 30 A0 C S 120 E 1

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Full Of Gold	Plating Semi-gold	INSULATOR MATERIAL: OF	LENGTH OF TERMINAL	PACKING
16: 1.6mm	2~50P	A0=0.8u"	B0=0.8U"	B: PA6T		A: PE Bag
20: 2.0mm		A1=1u"	B1=1U"	C: PA9T		B: Tape & Reel
25: 2.54mm		A2=1.5u"	B2=1.5U"	D: LCP		C: Tube
		A3=2u"	B3=2U"			D: Tube+CAP
		A4=3u"	B4=3U"			E: Tray
		A5=5u"	B5=5U"			
		A6=10u"	B6=10U"			
		A7=15u"	B7=15U"			
		A8=20u"	B8=20U"			
		A9=30u"	B9=30U"			
		S1=Ordinary Tin Plated				
		S2=Matte Tin Plated				
		S3=Tin-plated High-temperature				



				OPERATION		SCALE		Fit	 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.			
				X.X	±0.25	UNIT		MM				
				X.XX	±0.20	SIZE	A4	DESIGN	刘伟 2021.05.17	PART NO.	P320-2230A0CS120E1	
				X.XXX	±0.10							
				Angle	±3°	SHEET	1/1	CHECK		TITLE:	1.27排针 2*30P*2 L=12.0/2.5/3.0 180度 DIP端不能有毛边 H=2.0mm PA9T 镀普金 100/袋	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.		

1 2 3 4 5 6 7 8 9 10