

备注(Remark)
1. 材料(MATERIAL)
胶芯: LCP+30%G.F UL94V-0, 颜色: 黑色.
Housing: LCP+30%G.F UL94V-0, Color: Black
端子: 黄铜, 镍底30u"MIN, 镀黄金
Contact: Bronze, GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

额定电流: 3 AMP

Raring Current:3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.


Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage:AC 500V/Minute.



温度范围: -40°C to $+105^{\circ}\text{C}$

Temperture Range: -40° C to+105° C




Recommended P. C. B LAYOUT

General Tolerance ± 0.05



F185-11 10 A0 D RY F 1



				OPERATION		SCALE		Fit	 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM			
				X.XX	±0.20	SIZE	A4	DESIGN	李青杰2023. 04. 10	PART NO.	F185-1110A0DRYF1
				X.XXX	±0.10						
				Angle	±3°	SHEET	1/1	CHECK		TITLE:	2.54排母8.5mm塑高 1*10P 内径1.3 DIP:2.5 90度 Y型 LCP料 镀金足0.6U 700/卷 K8027
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.	