





6	7	8
REV	DESCRIPTION	APPR
0	原始图档	JACK
		Yang
		150815

Material
Insulator:Nylon 9T(UL94V-0)
TERMINAL:phosphor Bronze
TERMINAL:Plated Gold over
Nickel or Tin
Specification
Current rating:7A
instant CURRENT:10A
Contact Resistance:30MΩ
Insulation Resistance:100MΩ
Dielectric Voltage:500V
Operdting
Temperature:-40°~105°



Recommended P.C.B Layout

Layout Tolerance=+/-0.05mm

No. of Pins	Dimension	
	DIM.B	DIM.A
03	7.50	12.00
04	10.00	14.50
05	12.50	17.00
06	15.00	19.50
07	17.50	22.00
08	20.00	24.50
09	22.50	27.00
10	25.00	29.50

QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1		NUMBER:		东莞市文章济美电子有限公司				
<div><div>▽ ~0</div><div>▽ C ~0</div></div>		MM		INCH	MATERIAL:		HRC:		TITLE: Battery 2.5PH 90度DIP 左防呆 公座					
	.X	±0.25	.X	Ⓢ----	DRAWN BY		DATE							
	.XX	±0.15	.XX	Ⓢ----	JK-YANG				<div><div><div>THIRD ANGLE PROJECTION</div><div><div></div><div></div></div></div><div>料号: JME25M08-H58ZFDWZ-B</div></div>					
	.XXX	±0.05	.XXX	Ⓢ----	CHECKED BY		DATE							
	ANGULAR ±1°					APPROVED BY		DATE		PART NO.		DWG NO.		SHEET NO. 1/1
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS														