






Features :

- T-568A/B Dual wiring
- RJ45 complies with FCC part 68 standard
- Provides termination for 22~26 AWG wire
- Jack insertion life >750 mating cycles
- Operating temperature : -40°C~+60°C

Electrical :

- Contact resistance : 20m ohm
- DC Current rating : 1.5Amps
- DC resistance : Max.0.1 ohm
- Insulation Resistance : 500m ohm
- Dielectric withstanding voltage : 1000V



建议开孔尺寸:

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

MATERIAL	
CATEGORY	■ CAT.5E ■ CAT.6 ■ CAT.6A ■ CAT.7 □ CAT.8
HOUSING	ABS+PC UL94V-0
CONTACT	0.35mm THICKNESS PHOSPHOR BRONZE GOLD PLATED OVER NICKEL
GOLD-PLATING	□ 0.0762um/3u inch □ 0.15um/6u inch □ 0.38um/15u inch □ 0.76um/30u inch □ 1.27um/50u inch
COLOR	□ WHITE □ BLACK □ GREEN □ BLUE □ YELLOW □ RED □ ORANGE □ IVORY □ OTHER _____
TYPE OF PRODUCT	■ UNSHIELD ■ SHIELD : ZINC ALLOY, NICKLE PLATED.

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: RJ45 CAT.5E 直通连接头 带螺丝			
DRAWN: LYF	DATE: 2024-05-07	PART. NO.	R-RJ45Z08P-B005		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ45-0517	REV.	A ZJDZ