





RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	原始图档		JACK		150606

Material
Insulator:Nylon 9T(UL94V-0)
TERMINAL:phosphor Bronze
TERMINAL Plated:Gold over Nickel
or Tin
Specification
Current rating:7A
instant CURRENT:10A
Contact Resistance:30MΩ
Insulation Resistance:100MΩ
Dielectric Voltage:500V
Operdting Temperature:-40°~105°

No. of Pins	Dimension		
	DIM. A	DIM. B	DIM. C
02	7.00	2.50	7.0/8.0
03	9.50	5.00	7.0/8.0
04	12.00	7.50	7.0/8.0
05	14.50	10.00	7.0/8.0
06	17.00	12.50	7.0/8.0
07	19.50	15.00	7.0/8.0
08	22.00	17.50	7.0/8.0
09	24.50	20.00	7.0/8.0
10	27.00	22.50	7.0/8.0
11	29.50	25.00	7.0/8.0
12	32.00	27.50	7.0/8.0
13	34.50	30.00	7.0/8.0
14	37.00	32.50	7.0/8.0
15	39.50	35.00	7.0/8.0
16	42.00	37.50	7.0/8.0



Recommended P.C.B Layout
Layout Tolerance=+/-0.05mm

QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1	NUMBER:	东莞市文章济美电子有限公司			
<div>▽_A</div>		MM		INCH	MATERIAL:	HRC:					
	. X	±0.25	. X	Ⓜ	DRAWN BY DATE		TITLE: Battery 2.5PH 180度DIP 7.0/8.0H 公座				
	. XX	±0.15	. XX	Ⓝ							
	. XXX	±0.05	. XXX	Ⓞ	CHECKED BY DATE				<div> THIRD ANGLE PROJECTION</div> <div>料号: JME25M14-H70001A-B</div>		
	ANGULAR ±1°						APPROVED BY DATE				PART NO. DWG NO. SHEET NO. 1/1
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											
								A4			