

SPECIFICATION:

1.MATERIAL:

HOUSING:LCP 30% G/F UL 94V-0
COLOR:BLACK
CONTACT:BRASS C2680R-H,T=0.25mm
PEG: BRASS C2680R-H,T=0.30mm





2.FINISH:

CONTACT:1u",3u",5u",15u"GOLD PLATING ON CONTACT AREA
100u" MIN.TIN PLATING ON SOLDER TAILS
40u" MIN.NICKEL UNDERPLATING OVER ALL



3.ELECTRICAL:

CURRENT RATING:1.5 AMPERE PER CONTACT
CONTACT RESISTANCE:30 MILLIOHMS MAX
INSULATION RESISTANCE:1000 MEGOHMS MIN
DIELECTRIC WITH STANDING VOLTAGE:500 VDC
OPERATING TEMPERATURE: -40°C ~ +85°C

4.THE MARK (X) DIMENSIONS MUST BE MEASURED BY FAI.



PCB LAYOUT
TOLERANCES:±0.05MM



SECTION:Y-Y

环境要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Brass C2680		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED				
.X:±0.30	.X':±3"	APR. Alex	TITLE: SATA 7+15P 公座沉板式SMT H0.9 (半包式)	
.XX:±0.20	.XX':±2"	CHK. Jack	DWG NO. XY-SATA-22ACB-15G	
.XXX:±0.05	.XXX':±0.5"	DRA. Can	PROJ.	CUSTOMER DRAWING
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A	