





NOTE:

1. Operating Force: $180\text{gf} \pm 80\text{gf}$
2. Travel : $2.0 \pm 0.2\text{mm}$

NO.	Operating Type	Part No.
1	Push To Lock	K8-7071D-L1
2	Push No Lock	K8-7071D-N1



⑦	CAM STICK	—	1	SUS WIRE	NATURAL	—
⑥	TERMINAL	—	6	BRASS STRIP	Ag COATING	—
⑤	CASE	—	1	PA66	BLACK	—
④	COVER	—	1	POM	WHITE	—
③	SPRING	—	1	SUS	Natural	—
②	CONTACT	—	2	PBS	Ag CLAD	—
①	KNOB	—	1	POM	Blue	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS

DATE

DRAWN

LIANG

2026.03.19

CHECKED

TITLE:

PUSHBUTTON SWITCHES

APPROVALS

PART NO.

TOLERANCES ARE

30~以上
10~30
5~10
~ 5±0.30
±0.20
±0.15
±0.10

ANGLE

±2'

UNIT: mm

SCALE: 1:1

PROJ:

DRAWING NO.

—

SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.