




SPECIFICATION:
MATERIAL:
HOUSING: LCP 30% G/F UL 94V-0
COLOR: BLACK
CONTACT: PHOSPHOR BRONZE C2680 H,T=0.25mm
PEG: BRASS C2680R H,T=0.30mm
SHELL: spcc, T=0.30mm
FINISH:
CONTACT: G/F GOLD/TIN PLATING ON CONTACT AREA
100u" MIN. Matte TIN PLATING ON SOLDER TAILS
50u" MIN. NICKEL UNDERPLATING OVERALL
PEG: 100u" MIN. Matte TIN PLATING ON SOLDER TAILS
50u" MIN. NICKEL UNDERPLATING OVERALL
SHELL: 100u" MIN. Matte TIN PLATING ON SOLDER TAILS
50u" MIN. NICKEL UNDERPLATING OVERALL

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyecom Electronics Co., Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: SATA 7P公座双柱AB型 带铁壳成品	
.X:±0.30	.X*:±3°	CHK.	Jack	DWG NO. XY-SATA-7AZC-04G	
.XX:±0.20	.XX*:±2°	DRA.	Can	PROJ.	CUSTOMER DRAWING
.XXX:±0.05	.XXX*:±0.5°	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A