







This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior concert&that no right is granted to disclose or to use any information in this document.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	INITIAL RELEASED	2026.10.15	JASON

RoHS
Compliant



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

备注:

1.材质:

1.1 胶芯: LCP+30%G.F UL94V-0

1.2 端子: 高导电C7025,

1.3 外壳: SUS304,

1.4 中夹片: SUS301,

2.主要特性:

2.1额定电流: 5A

2.2接触阻抗: 40mΩ MAX(初始值)

50mΩ MAX(测试后)

2.3绝缘阻抗: 100MΩ MIN

2.4耐压测试: 100V AC R.M.S.

2.6整体插入力: 5-20N 整体插入力: 5-20N (耐久后)

整体拔出力: 8-20N 整体拔出力: 5-20N (耐久后)

2.7耐久: 10000次

2.8耐高温: SMT 回流焊 (峰值260°±5°), 塑胶不能有起泡,

融胶等不良, 变色, 翘曲变形在公差范围内;

2.9产品须做焊锡测试, 粘锡面积达到95%以上;

3.0盐雾测试: 24H MIN(外壳盐雾48H, 端子24H除焊脚预断位)

3.1工作温度: -30℃~+85℃

P/N: 101055-211010

CONTACT AREA PLATED

01: Au G/F

SOLDER AREA PLATED

1: Au G/F

PACKAGING

1: REEL PACKAGING


PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	SSTXp1	B11	SSRXp1
A3	SSTXn1	B10	SSRXn1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXn2	B3	SSTXn2
A11	SSRXp2	B2	SSTXp2
A12	GND	B1	GND

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA®深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10°	PART NO.	TITLE: TYPE C 24P 板上单排贴板			
.XX ±0.20	.X.* ± 8°	SEE P/N				
.XXX ±0.10	.XX.* ± 5°	DESIGN: JASON	DRAWG NO.			
UNIT	mm		C-101055			
MATERIAL	---	CHED: CHECK				
FINISH	---	APPD: ARAY				
			SCALE	SHEET	REV.	
			1:1	1/2	A	


This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior concert&that no right is granted to disclose or to use any information in this document.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	INITIAL RELEASED	2026.10.15	JASON

RoHS
Compliant



包装示意图:



备注

- 1.把上下载带送入载带机进行调整,然后将产品按照指定的方式摆入下载带中,开动卷带机进行卷装(每卷包1000PCS),卷装
- 2.在卷装OK的每卷盘面的指定位置上贴上物料标签装入纸箱内;每箱装10盘
- 3.纸箱用封箱带将其封好,胶带要求工字型,不可遮住标签;
- 4.上载带剥离力:0.2-1.2N.;

	REEL	CARTON
CONNECTOR (PCS)	1000	10000

TOLERANCE	NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10°	PART NO.	TITLE: TYPE C 24P 板上单排贴板		
.XX ±0.20	.X.* ± 8°	SEE P/N			
.XXX ±0.10	.XX.* ± 5°	DESIGN: JASON	DRAWG NO. C-101055		
UNIT	mm	CHED: CHECK			
MATERIAL	---	APPD: ARAY			
FINISH	---				
			SCALE	SHEET	REV.
			1:1	2/2	A