








RoHS
Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		



PC Edge
RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm



B12	GND
B9	VBUS
B5	CC2
A5	CC1
A9	VBUS
A12	GND
PIN	SIGNAL NAME

X.	±0.50	X.*	±2°
.X	±0.30	.X.*	±1°
.XX	±0.10	.XX.*	±0.5°
.XXX	±0.05		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD			

UNITS	mm
MAT'L	/
FINISH	/
Q'TY	/

广东创粤科技有限公司			
TITLE: USB TYPE C 6PIN 沉板1.6-12.0H			
APPD:	DWG NO:		
CHKD:	TYPE-C-6P-R1.6L12.0-24310		
DR:	SCALE SHEET REV.		
1/1 1/1 A1			

注意:

1. 材料”

成型: LCP UL94 V-0

触点: 铜合金。

最小接触面积镀金, 0.5u “

焊料区的最小锡 (无铅),

壳体: SUS304-H/CU, T=0.25±0.03mm

50u “镀镍。

2. 机械:

插入: 5~20N。

拔取: 试验后8~20N。

耐久性: 5000次循环

3. 电气:

电流: VBUS为3A;

接地引脚为1.25A

其他0.25A。

电压: 最大20 V

耐压: 100V AC R.M.S。

接触电阻: 最大40mΩ。

绝缘电阻: 最小100MΩ。

4. 环境

温度范围-25° C~+85° C